


Metric



elesa
Original design I.222 N

Metric table

Dimensions in: millimeters / inches

¹ d_1	² d_2 Bore	d_3	h	t
15 0.59	B 6	12 0.47	25 0.98	17 0.67
20 0.79	B 8	14 0.55	31 1.22	21 0.83
26 1.02	B 10	17 0.67	42 1.65	30 1.18
33 1.30	B 10	20 0.79	54 2.13	37 1.46
33 1.30	B 12	20 0.79	54 2.13	40 1.57
38 1.50	B 14	23 0.91	68 2.68	50 1.97
41 1.61	B 16	25 0.98	87 3.43	58 2.28

Specification

Handle

- Plastic, Phenolic (PF)
- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish

Bushing

- Polyamide (PA)
- Embedded

RoHS

Domed gear lever knobs EN 719.1 satisfy by their form and ergonomical aspects. By using these knobs a threaded end on a lever is not required. These knobs are mounted by using a plastic hammer to drive them over a shaft end which should preferably be slightly rounded or chamfered (30°). The bushing is embedded during the manufacturing process and it does not need insertion before driving it over a shaft.

see also...

	Page
EN 719.2 Domed Gear Lever Knobs (Tapped or Press-On Type)	QVX
EN 719 Domed Gear Lever Knobs (with Tapped Hole)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

EN 719.1-33-B10

- ¹ Handle diameter d_1
- ² Bore d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

