



SS Stainless Steel

3 Type

C With pull ring, lock-out

Metric table

Dimensions in: millimeters - inches

1 d ₁ Pin -0.05 Bore +0.1 -0.3	2 s	d ₂ +0.3	d ₃	d ₄	h ₁	h ₂	l ₁ ≈	l ₂	l ₃	l ₄ ≈	l ₅	l ₆	m	A/F in mm	Spring load ≈	
															Initial	End
8	20	6.1	34	6	7.5	1.5	68	14	35	51	41.5	48	34	10	14 N	35 N
0.31	0.79	0.24	1.34	0.24	0.30	0.06	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
10	20	6.1	34	6	7.5	1.5	68	14	35	51	41.5	48	34	10	14 N	35 N
0.39	0.79	0.24	1.34	0.24	0.30	0.06	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
12	20	6.1	34	6	7.5	1.5	68	14	35	51	41.5	48	34	10	14 N	35 N
0.47	0.79	0.24	1.34	0.24	0.30	0.06	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
14	20	6.1	34	6	7.5	1.5	68	14	54	51	41.5	48	34	10	14 N	35 N
0.55	0.79	0.24	1.34	0.24	0.30	0.06	2.68	0.55	2.13	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
16	30	10.1	48	9	15	5	102	20	54	78	60	80	55	17	22 N	70 N
0.63	1.18	0.40	1.89	0.35	0.59	0.20	4.02	0.79	2.13	3.07	2.36	3.15	2.17		4.95 lbf	15.74 lbf
20	30	10.1	48	9	15	5	102	20	54	78	60	80	55	17	22 N	70 N
0.79	1.18	0.40	1.89	0.35	0.59	0.20	4.02	0.79	2.13	3.07	2.36	3.15	2.17		4.95 lbf	15.74 lbf

Specification

- Body
Steel precision casting
- Zinc plated, blue passivated finish **ZB**
- Zinc plated and powder coated
Black, RAL 9005, textured finish **SW**
- Body
Stainless steel
precision casting AISI 316 **A4**
- Pull ring
- Steel precision casting
Zinc plated, blue passivated finish
(for ZB and SW)
- Stainless steel
precision casting AISI 316 (for A4)
- Plunger Pin
- Steel, zinc plated, blue passivated finish
(for ZB and SW)
- Stainless steel AISI 316 (for A4)
- Spring
Stainless steel AISI 316Ti
- Load Rating Information → page 2103
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

With GN 722.5 indexing plungers, the plunger pin is actuated via the pull ring. This is done either manually, with a cable or by means of an extended pull rod with hook. The **ZB** and **ST** version is designed for applications in steel construction, whereas the stainless steel version **A4** is suitable for use in particularly aggressive environments.

The type with rest position is used when the plunger pin should temporarily not protrude. For this purpose, the pull ring is turned sideways after the locking pin has been retracted. The ring is held in this position by the catch recess at the top of the guide.

The dimensional tolerances between plunger pin and body are selected so that the functional reliability is guaranteed even with rough applications or in case of contamination.

There are several options for fastening. The hexagonal mounting holes allow the use of DIN 912 socket cap screws and hex screws or nuts according to DIN 931 or DIN 934.

see also...

- List of Indexing Plunger Types → page 916
- Square Cam Action Spring Latches GN 722.2 (with Mounting Flange) → page 1013
- Locating Bushings GN 412.2 / GN 412.4 → page 996

<p>How to order</p> <p>GN 722.5-16-30-C-ZB</p>	1 Pin diameter d ₁
	2 Square s
	3 Type
	4 Finish (Material)