



3 Type

C With pull ring, lock-out

Metric table

1 2

Dimensions in: millimeters - inches

d1 Pin -0.05 +0.1	s	b +0.3	d2 +0.3	d3	d4	h1	h2	k1	k2	k3	l1 ≈	l2	l3	l4 ≈	l5	l6	m	A/F in mm	Spring load ≈	
																			Bore +0.1 +0.3	Initial
8	20	6.1	6.1	34	6	7.5	1.5	7.5	18	12	68	14	35	51	41.5	48	34	10	14 N	35 N
0.315	0.79	0.240	0.240	1.34	0.24	0.30	0.06	0.30	0.71	0.47	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
10	20	6.1	6.1	34	6	7.5	1.5	7.5	18	12	68	14	35	51	41.5	48	34	10	14 N	35 N
0.394	0.79	0.240	0.240	1.34	0.24	0.30	0.06	0.30	0.71	0.47	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
12	20	6.1	6.1	34	6	7.5	1.5	7.5	18	12	68	14	35	51	41.5	48	34	10	14 N	35 N
0.472	0.79	0.240	0.240	1.34	0.24	0.30	0.06	0.30	0.71	0.47	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
14	20	6.1	6.1	34	6	7.5	1.5	7.5	18	12	68	14	35	51	41.5	48	34	10	14 N	35 N
0.551	0.79	0.240	0.240	1.34	0.24	0.30	0.06	0.30	0.71	0.47	2.68	0.55	1.38	2.01	1.63	1.89	1.34		3.15 lbf	7.87 lbf
16	20	10.1	10.1	48	9	15	5	14	34	10	102	20	54	78	60	80	55	17	22 N	70 N
0.630	0.79	0.398	0.398	1.89	0.35	0.59	0.20	0.55	1.34	0.39	4.02	0.79	2.13	3.07	2.36	3.15	2.17		4.95 lbf	15.74 lbf
20	20	10.1	10.1	48	9	15	5	14	34	10	102	20	54	78	60	80	55	17	22 N	70 N
0.787	0.79	0.398	0.398	1.89	0.35	0.59	0.20	0.55	1.34	0.39	4.02	0.79	2.13	3.07	2.36	3.15	2.17		4.95 lbf	15.74 lbf

Specification

4

- Body
Steel precision casting
- Zinc plated, blue passivated finish **ZB**
- Zinc plated and powder coated
Black, RAL 9005, textured finish **SW**
- Body
Stainless steel
precision casting AISI 316 **A4**
- Pull ring
- Steel precision casting
Zinc plated, blue passivated finish
(for ZB and SW)
- Stainless steel
precision casting AISI 316 (for A4)
- Plunger Pin
- Steel, zinc plated, blue passivated finish
(for ZB and SW)
- Stainless steel AISI 316 (for A4)
- Spring
Stainless steel AISI 316Ti
- Load Rating Information → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS

Information

With indexing plungers GN 722.6, the plunger pin is actuated via the pull ring. This is done either manually, with a cable or by means of an extended pull rod with hook. The **ZB** and **ST** version is designed for applications in steel construction, whereas the stainless steel version **A4** is suitable for use in particularly aggressive environments.

The type with rest position is used when the plunger pin should temporarily not protrude. For this purpose, the pull ring is turned sideways after the locking pin has been retracted. The ring is held in this position by the catch recess at the top of the guide.

The dimensional tolerances between plunger pin and body are selected so that the functional reliability is guaranteed even with rough applications or in case of contamination.

For fastening, slotted or hexagonal mounting holes allow the use of socket cap screws DIN 912 and hex screws or nuts according to DIN 931 or DIN 934.

see also...

- List of Indexing Plunger Types → page QVX

<p>How to order</p> <p>GN 722.6-12-20-C-SW</p>	1 Pin diameter d ₁
	2 Square s
	3 Type
	4 Finish (Material)