



- 3 Type**
- N** Cover neutral
  - M** Cover with indicator point
- 4 Identification no.**
- 1** With set screw
  - 2** With collet

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> H8 Bore		<b>2</b> d <sub>3</sub> Collet	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	Length l	t
22 0.87	B 5	-	-	16 0.63	14 0.55	M 4	15 0.59	9 0.35	4.3 0.17	5 0.20	-
27 1.06	B 6	-	Z 6	20 0.79	18 0.71	M 4	17 0.67	11 0.43	4.3 0.17	5.5 0.22	14 0.55
34 1.34	B 6	B 8	Z 8	25 0.98	23 0.91	M 5	20 0.79	14 0.55	4.2 0.17	7 0.28	17 0.67
42 1.65	B 8	B 10	Z 10	32 1.26	30 1.18	M 5	23 0.91	17 0.67	4 0.16	8.5 0.33	20 0.79

**Specification**

- Body  
Aluminum  
Black anodized finish
- Cover  
Plastic, light gray
- Collet / hex nut  
Brass
- Socket set screw DIN 916  
Stainless steel  
With internal hex and serrated point
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

The light gray cover makes these GN 726 control knobs very attractive. The cover is held in place by firmly pushing it into the recess. It can be removed by inserting a screw driver into the slot provided.

The collet type provides a simple way of positioning and locking the control knob to the shaft.

Because they are made from an aluminum extrusion, manufacturing specials in existing diameters can be done at relatively low cost.

see also...

- Knurled Control Knobs GN 726.1 (Aluminum) → page 331
- Knurled Control Knobs EN 526 (Technopolymer Plastic) → www.jwwinco.com
- Control Knob Flanges GN 826 (for Adjustable Spindles) → www.jwwinco.com

How to order	
<b>1</b>	Outside diameter d <sub>1</sub>
<b>2</b>	Collet d <sub>3</sub> (Bore d <sub>2</sub> )
<b>3</b>	Type
<b>4</b>	Identification no.

**GN 726-34-Z8-M-2**