



3 Type

- A** With arrow
- B** Neutral, without indicator point or scale
- S** With scale 0...9, 20 graduations

4 Identification no.

- 1** With set screw
- 2** With collet

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ H8 Bore		2 d ₃ Collet	d ₄	d ₅	d ₆	d ₇	h ₁	h ₂	h ₃	h ₄	Length l	t
22 0.87	B 5	-	-	16 0.63	14 0.55	M 4	27.5 1.08	22 0.87	16 0.63	4.3 0.17	8 0.31	12.5 0.49	-
27 1.06	B 6	-	Z 6	20 0.79	18 0.71	M 4	33.5 1.32	26 1.02	20 0.79	4.3 0.17	9 0.35	14 0.55	14 0.55
34 1.34	B 6	B 8	Z 8	25 0.98	23 0.91	M 5	41 1.61	30 1.18	24 0.94	4.2 0.17	10 0.39	15 0.59	17 0.67
42 1.65	B 8	B 10	Z 10	32 1.26	30 1.18	M 5	50 1.97	34 1.34	28 1.10	4 0.16	11 0.43	16 0.63	20 0.79

Specification

- Body
Aluminum
Black, anodized finish
- Skirt
Plastic
- Black
- Pressed-on
- Arrow (Type A) and scale (Type S)
White, laser engraved
- Cover
Plastic, light gray
- Collet / hex nut
Brass
- Socket set screw DIN 916
Stainless steel
With internal hex and serrated point
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

On request

- Special graduations, see
"How to Order Graduations" → page 328

Information

The light gray cover makes these GN 726.2 control knobs an aesthetically pleasing choice. The cover is held in place by firmly pushing it into the recess. It can be removed by inserting a screw driver into the slot provided.

The collet type provides a simple way of positioning and locking the control knob to the shaft.

Other types than the standard scale can be supplied, see order examples on „How to Order Graduations“.

see also...

- Knurled Control Knobs GN 723.4 (Aluminum) → www.jwwinco.com
- Control Knob Flanges GN 826 (for Adjustable Spindles) → www.jwwinco.com

<p>How to order</p> <p>GN 726.2-27-Z6-S-2</p>	1	Outside diameter d ₁
	2	Collet d ₃ (Bore d ₂)
	3	Type
	4	Identification no.