



Metric



elesa

Original design M.343-SOFT



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table

Dimensions in: millimeters / inches

1	2	2									
$l_1 \pm 0.5$	d_1 Type A	d_2 Type B	a	b	d_3	h_1	h_2	l_2	l_3	t_1 min.	t_2
132 5.20	M 6	6.4 0.25	16 0.63	26 1.02	10.5 0.41	53 2.09	15 0.59	148 5.83	116 4.57	12 0.47	8.5 0.33
132 5.20	M 8	-	16 0.63	26 1.02	-	53 2.09	15 0.59	148 5.83	116 4.57	12 0.47	8.5 0.33

Specification

Handle

- Plastic, polypropylene (PP)
- Black-gray, matte finish, similar to RAL 7021
- Brass tapped insert

Insert with finger recesses

- Plastic, thermoplastic elastomer (TPE)
- Chemically bonded to the base body
- Operating temperature 32 °F to 176 °F (0 °C to +80 °C)
- Color
 - Orange, RAL 2004, matte finish
 - Gray, RAL 7024, matte finish
 - Red, RAL 3000, matte finish
 - Green, RAL 6017, matte finish
- Hardness 70 Shore A

- **OR**
- **GR**
- **RT**
- **GN**

RoHS

Cabinet U-handles EN 725.3 are characterized by their stability and their ergonomic design. The soft finger recesses (Softline product family) on the underside of the handle provide a particularly pleasant feel when gripping. Cabinet U-handles EN 725.3 can be installed from the rear (type A) as well as from the operating side (type B).

see also...

	Page
GN 328 Cabinet U-Handles (Aluminum)	QVX
EN 528 Cabinet U-Handles (Plastic)	QVX
EN 628 Bridge Handles (Plastic)	QVX
GN 565.1 Cabinet U-Handles (Aluminum)	QVX

Technical Information

Product Family Softline	QVX
Strength Values	QVX
Plastic Characteristics	QVX

How to order

1	Length l_1
2	Thread d_1 (Diameter d_2)
3	Type
4	Insert color

EN 725.3-132-M8-A-RT