



Metric table

1

Dimensions in: millimeters / inches										
l_1	h_1	h_2	l_2	l_3	l_4	l_5	$l_6 + 1$	$l_7 + 1$	m_1	m_2
127 5.00	80 3.15	43 1.69	72 2.83	25 0.98	3.5 0.14	22.5 0.89	60 2.36	88 3.46	100 3.94	53 2.09
155 6.10	80 3.15	43 1.69	99 3.90	25 0.98	3.5 0.14	22.5 0.89	60 2.36	115 4.53	128 5.04	53 2.09

4

Specification

Handle

Zinc die-cast

Powder coated

• Black, RAL 9005, textured finish

• Silver, RAL 9006, textured finish

Housing seal (Identification no. 2)

Rubber NBR

• Black

• Glued

Countersunk sealing screws DIN 7991-M5x16

(Type A, identification no. 2)

Stainless steel A2

Polyamide coating on head

Set screws (Type C)

Stainless steel AISI 304

Molded-in

Protection class IP 66

RoHS

SW

SR

see also...

GN 7332 Gripping Trays (Stainless Steel)

EN 733 Gripping Trays (Plastic, Screw-In Type)

EN 731 Gripping Trays (Plastic, Clip-In Type)

Page

QVX

QVX

QVX

Technical Information

IP Protection Classes

Stainless Steel Characteristics

QVX

QVX

How to order

1

2

3

4

GN 7330-127-A-2-SW

1 Length l_1

2 Type

3 Identification no.

4 Finish

www.jwwinco.com | 1-800-877-8351

WARNING: Cancer and Reproductive Harm

www.P65Warnings.ca.gov

197