



Metric table

2

$l_1$	a	$b_1$	$b_2$	$b_3$	d	$h_1$	$h_2$	$l_2$	t min.
120 4.72	10 0.39	6 0.24	12.5 0.49	35 1.38	M 6	32 1.26	25 0.98	100 3.94	9 0.35

Dimensions in: millimeters - inches

Specification

13

- Stainless steel precision casting AISI 316 Matte shot-blasted finish
- Stainless Steel Characteristics → page 2143
- RoHS compliant

A4

GS

On request

- Polished or powder coated version
- Various metric size fasteners and kit packaging

Information

The GN 730.5 ledge handle is used on doors, guards and hatches on machines, as well as on drawers and pull-out units. Due to the material used, the handle is intended especially for use in corrosive environments with aggressive media.

The ledge handle is made in a way that does not allow pooling of fluids, which makes cleaning easier and prevents build-up of residue and bacteria.

It is attached from the back side via the mounting threads. Alternatively, the handle can be welded from the front.

see also...

- Ledge Handles GN 730 (Aluminum) → page 190
- Ledge Handles GN 430 / GN 430.1 (Aluminum) → page 188