



2 Bore code

- B** Without keyway
- K** With keyway
- Z** With collet

4 Type

- A** Without handle
- D** With revolving handle

Metric table

Dimensions in: millimeters - inches

| 1 d_1 | 3 d_2 H8 Bore | d_3 | d_4 | d_5 | $b-0.5$ | h | l_1 | l_2 | $l_3 \approx$ | r | \emptyset Handle |
|----------------|------------------------|------------|------------|--------------|------------|-------------|------------|------------|---------------|--------------|--------------------|
| 52 2.05 | 10 0.39 | 22 0.87 | 37 1.46 | 39.5 1.56 | 13 0.51 | 3.8 0.15 | 23 0.91 | 17 0.67 | 19 0.75 | 15.5 0.61 | 13 0.51 |
| 62 2.44 | 10 0.39 | 25 0.98 | 47 1.85 | 49.5 1.95 | 13 0.51 | 3.8 0.15 | 23 0.91 | 17 0.67 | 21 0.83 | 20.5 0.81 | 14 0.55 |

Specification

- Aluminum
Black, anodized finish
- Cover
Plastic, light gray
- Collet / hex nut
Brass
- Set screw DIN 916
Stainless steel
With internal hex and serrated point
- Cylindrical revolving handle GN 599.5
→ page 41
Plastic
Technopolymer
- Black, matte finish
- Threaded spindle
Stainless steel AISI 303
- Cross Holes GN 110 → page 2042
- Keyways WN / DIN 6885 → page 2039 / 2040
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Other modifications such as inch and special metric bores, keyways, set screw holes, etc.

Information

GN 736 knurled control knobs are used for setting operations with low torque. Coarse setting is made by means of the cylindrical revolving handle (fingertip grip) followed by fine setting using the knurled rim of the knob. All control knobs are produced with an ergonomically shaped and attractively designed rim. No mounting hole in rim for control knob without handle. Handle shipped loose; mounting of handle is required.

see also...

- Knurled Control Knobs EN 735 (Technopolymer Plastic) → www.jwwinco.com
- Countersunk Washers GN 184 (for Axial Fixing) → page 1150
- Control Knob Flanges GN 826 (for Adjustable Spindles) → www.jwwinco.com
- Knurled Control Knobs GN 226 (Technopolymer Plastic) → page 275

| How to order | |
|------------------------------|--|
| 1 Knob diameter d_1 | |
| 2 Bore code | |
| 3 Bore diameter d_2 | |
| 4 Type | |

GN 736-52-B10-A