


Application example



Metric table

										Dimensions in: millimeters - inches		
¹ m ₁	² h ₁	b	d ₁	d ₂	d ₃	d ₄	h ₂	m ₂	Length l	For toggle clamp size		
										GN 810 GN 810.1 GN 810.3 GN 810.4	GN 820 GN 820.1 GN 820.2 GN 820.3 GN 820.4	GN 860
82 3.23	16 0.63	19.5 0.77	6.2 0.24	M 6	9.2 0.36	12 0.47	37 1.46	22 0.87	91 3.58	130	130	125
100 3.94	18 0.71	26 1.02	8 0.31	M 8	12 0.47	16 0.63	43 1.69	27 1.06	112 4.41	230	230	200

Specification

- Steel, zinc plated, blue passivated finish **ST**
- RoHS compliant

Information

GN 801.2 clamping arm extenders are used together with toggle clamps with "U-bar clamping arm" to clamp something simultaneously at two points in parallel, such as with spindle assemblies. These are mounted to the clamping arm and affixed in the desired position along the slot.

The side position of the clamping screws is adjusted via joints that enable any positioning of the spindle assemblies. A symmetrical placement creates a balanced clamping result.

All parts are supplied in a non-assembled set. Four flanged washers are included for fastening the spindle assembly.

see also...

- Clamping Arm Extenders GN 801.1 (Rigid) → page 860
- Clamping Arm Extenders GN 809.1 → page 862
- Toggle Clamp Spindle Assemblies GN 804 → page 856
- Toggle Clamp Spindle Assemblies GN 807 → page 857

How to order GN801.2-82-16-ST	¹ Length m ₁
	² Height h ₁
	³ Material