



Metric table

1

Dimensions in: millimeters - inches

$l_1$	$b_1$	$b_2$	$b_3$	$h_1$	$h_2$	$l_2$	$l_3$
115 4.53	58 2.28	31 1.22	43.5 1.71	19 0.75	3 0.12	91 3.58	94 3.70

Specification

- 2
- Plastic  
Technopolymer (Polyamide PA)
    - Glass fiber reinforced
    - Temperature resistant up to 176 °F (80 °C)
  - Color (matte finish):
    - Black-gray, RAL 7021
    - White, RAL 9002
  - Plastic Characteristics → page 2135
  - RoHS compliant



On request

- Self-extinguishing plastic (SV) 

Information

EN 739.1 gripping trays are useful for opening and closing sliding doors.

No mounting screws are required for assembling the recessed grips. The installation opening for the gripping tray must be created according to the dimensions given in the table.

The gripping tray is mounted by first inserting it into the opening on the firmly toothed side and then pressing it in against the opposite side until the locking elements clip into place.

Dimensions in: millimeters - inches

Wall thickness $s$	$x + 0.2$	$y + 0.2$
0.7 ... 1 0.03 ... 0.04	51.5 2.03	105.3 4.15
> 1 ... 1.5 > 0.04 ... 0.06	51.7 2.04	105.3 4.15
> 1.5 ... 2.2 > 0.06 ... 0.09	52 2.05	105.3 4.15

How to order

1 2

EN 739.1-115-SG	1 Length $l_1$
	2 Color