



3 Type

- A Without dipstick
- B With dipstick

4 Identification no.

- 1 Without vent hole
- 2 With vent hole

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ +0.2	d ₃ Vent hole	l ₁	l ₂	l ₃	l ₄	l ₅
30 1.18	20 0.79	2 0.08	14 0.55	29 1.14	6.5 0.26	10.5 0.41	188 7.40
35 1.38	26 1.02	2 0.08	14 0.55	29 1.14	6.5 0.26	10.5 0.41	188 7.40

Specification

- Body
Plastic
Technopolymer (Polypropylene PP)
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- O-ring
Rubber NBR (Perbunan®)
- Dipstick
Steel, phosphate-treated
- *Elastomer Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

On request

- Fluid level markings / special lengths
see GN 109 → page QVX

Information

EN 748 fluid fill plugs do not require a thread for assembly. The minimum wall thickness of the container is 6.5 mm (l₃).

The dipstick has two flat sides on which the MIN-MAX markings can easily be applied (see GN 109 → page QVX).

How to order	1 Diameter d ₁
EN 748-30-20-B-1	2 Bore diameter d ₂
	3 Type
	4 Identification no.