



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

² d_1		³ d_2		d_3	d_4	l_1	l_2	$l_3 \approx$	l_4
KT	NI								
16 0.63	-	M 6	-	10 0.39	13 0.51	41.5 1.63	12 0.47	2.5 0.10	15 0.59
18 0.71	18 0.71	M 6	M 8	10 0.39	14.5 0.57	56 2.20	13 0.51	2.5 0.10	19 0.75
22 0.87	22 0.87	M 8	M 10	14 0.55	18.5 0.73	59 2.32	14 0.55	2.5 0.10	21 0.83
24 0.94	24 0.94	M 8	M 10	14 0.55	18.5 0.73	74 2.91	16 0.63	2.5 0.10	27 1.06
25 0.98	-	M 10	-	16 0.63	20 0.79	84 3.31	16 0.63	2.5 0.10	30 1.18

Specification

- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 194 °F (90 °C)
- Black, matte finish
- Stainless steel AISI 303 **NI**
Fine turned, plain finish
- Threaded spindle
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

Information

GN 798.1 stepped cylindrical revolving handles are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

- *Stepped Retractable Handles GN 798.5 (with Locking Mechanism)* → page 48

How to order

¹ ² ³
GN 798.1-KT-16-M6

- 1** Material
- 2** Handle diameter d_1
- 3** Thread d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4