



SS Stainless Steel

Metric table

1

Dimensions in: millimeters - inches

Size	F _H Holding capacity	b ₁	b ₂	b ₃ -0.5	b ₄	b ₅	b ₆	d ₁	d ₂	h ₁
100	1000 N 225 lbf	28 1.10	15 .59	12 .47	41 1.61	19 .75	36 1.42	3 .12	4.3 .17	17 .67

Size	h ₂	l ₁ ≈	l ₂	l ₃ ≈	m ₁	m ₂	m ₃	m ₄	r ≈
100	13 .51	114 4.49	72 2.83	40 1.57	7 .28	15.5 .61	5 .20	15 .59	37 1.46

Specification

2

- Toggle latch
Steel, zinc plated, blue passivated finish **ST**
- Stainless steel AISI 304 **NI**
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Information

GN 832.3 toggle latches are used for the secure holding of flaps, container lids, etc. They lock securely over the center and are thus vibration proof.

The components to be linked are held in position by the elasticity of the hook latch.

The load specified in the table is simply a guideline value for the nominal static pulling force the latch can withstand. The holding capacity can be adversely affected by the conditions under which the latch is used, such as vibration or shock loads.

The catch bracket is included.

How to order

GN 832.3-100-NI

- 1 Size
- 2 Material