



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁		d ₂	d ₃	d ₄	l ₁	l ₂	l ₃ ≈	l ₄	s
KT	NI	Thread							
16 0.63	-	M 6	10 0.39	13 0.51	41.5 1.63	12 0.47	4 0.16	15 0.59	8 0.31
18 0.71	18 0.71	M 6	10 0.39	14.5 0.57	56 2.20	13 0.51	4 0.16	19 0.75	8 0.31
22 0.87	22 0.87	M 8	14 0.55	18.5 0.73	59 2.32	14 0.55	5.2 0.20	21 0.83	11 0.43
24 0.94	24 0.94	M 10	14 0.55	18.5 0.73	74 2.91	16 0.63	5.2 0.20	27 1.06	11 0.43
25 0.98	-	M 10	16 0.63	20 0.79	84 3.31	16 0.63	5.5 0.22	30 1.18	13 0.51

Specification

- Plastic Technopolymer (Polyamide PA) **KT**
 - Temperature resistant up to 194 °F (90 °C)
 - Black, matte finish
- Stainless steel AISI 303 **NI**
 - Fine turned
- Threaded spindle
 - Stainless steel AISI 303
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 798.4 stepped cylindrical revolving handles are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

- Stepped Retractable Handles GN 798.5 (with Stainless Steel Locking Mechanism) → page 48

How to order

GN 798.4-KT-16-M6

- 1 Material
- 2 Handle diameter d₁
- 3 Thread d₂