



Inch | Metric



SS Stainless Steel

3 Type

- E** With tapped blind bore
- D** With tapped through bore

Inch table

Dimensions in: inches / millimeters

1 d_1	2 d_2	d_3	d_4	b	h_1	h_2	t_1 min.	t_2
1.81 46	1/4 x 20	0.51 13	0.26 6.5	0.24 6	0.89 22.5	0.24 6	0.47 12	0.39 10
1.81 46	5/16 x 18	0.51 13	0.33 8.5	0.24 6	0.89 22.5	0.24 6	0.59 15	0.51 13
2.28 58	5/16 x 18	0.63 16	0.33 8.5	0.28 7	1.04 26.5	0.28 7	0.59 15	0.51 13
2.28 58	3/8 x 16	0.63 16	0.41 10.5	0.28 7	1.04 26.5	0.28 7	0.71 18	0.63 16

Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2	d_3	d_4	b	h_1	h_2	t_1 min.	t_2
46 1.81	M 6	13 0.51	6.5 0.26	6 0.24	22.5 0.89	6 0.24	12 0.47	10 0.39
46 1.81	M 8	13 0.51	8.5 0.33	6 0.24	22.5 0.89	6 0.24	15 0.59	13 0.51
58 2.28	M 8	16 0.63	8.5 0.33	7 0.28	26.5 1.04	7 0.28	15 0.59	13 0.51
58 2.28	M 10	16 0.63	10.5 0.41	7 0.28	26.5 1.04	7 0.28	18 0.71	16 0.63

Specification

Stainless steel precision casting AISI CF-8
Matte shot-blasted finish **MT**
RoHS

Technical Information

Stainless Steel Characteristics **QVX**

The ridges on the wings of wing nuts GN 834 permit a better grip.

see also...

	Page
GN 432 Wing Nuts	QVX
GN 434 Wing Nuts	QVX
GN 5345 Three-Lobed Knobs	QVX
DIN 6335 Hand Knobs	QVX

How to order (Inch)

1	Handle diameter d_1
2	Thread d_2
3	Type
4	Finish

GN 834-58-3/8X16-E-MT

How to order (Metric)

1	Handle diameter d_1
2	Thread d_2
3	Type
4	Finish

GN 834-46-M8-D-MT

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

