



2 Type
E For single joints
D For double joints

Metric table

Dimensions in: millimeters - inches

d ₁ Joint Ø	d ₂ Type E	d ₃ Type E	d ₄ Type D	d ₅ Type D	l ₁ Type E	l ₂ Type D
16 0.63	15 0.59	28 1.10	16 0.63	35 1.38	34 1.34	55 2.17
22 0.87	20.5 0.81	40 1.57	20 0.79	36 1.42	45 1.77	65 2.56
25 0.98	24.5 0.96	48 1.89	24 0.94	44 1.73	50 1.97	70 2.76
28 1.10	27.5 1.08	52 2.05	28 1.10	51 2.01	56 2.20	80 3.15
32 1.26	30.5 1.20	56 2.20	32 1.26	62 2.44	65 2.56	90 3.54
36 1.42	35.5 1.40	66 2.60	-	-	72 2.83	-
42 1.65	40 1.57	75 2.95	40 1.57	73 2.87	82 3.23	120 4.72
45 1.77	45 1.77	84 3.31	-	-	95 3.74	-
50 1.97	50 1.97	92 3.62	50 1.97	90 3.54	108 4.25	155 6.10
58 2.28	56 2.20	100 3.94	-	-	122 4.80	-

Specification

- Single joint boot
 - Type E
 - Neoprene rubber (CR)
 - Black
- Double joint boot
 - Type D
 - Smooth PVC elastomer plastic
 - Black
- *Elastomer Characteristics* → page 2135
- **RoHS compliant**

Information

GN 808.1 cover boots provide universal joints protection against dirt, dust and other debris. They can also be filled with grease, which gives long term lubrication for friction bearings. The cover boots are secured at each end with two cable ties, supplied but not assembled.

see also...

- *Universal Joints with Friction Bearing DIN 808 (Steel, Plain Finish)* → page 1726
- *Universal Joints with Friction Bearing DIN 808 (Stainless Steel)* → page 1728

How to order GN 808.1-25-E	1	Joint diameter d ₁
	2	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10