



Metric table

Dimensions in: millimeters - inches

¹ b	² d ₁ F9 Bore				d ₂	l ₁	l ₂	l ₃	l ₄	l ₅	m ₁	m ₂	m ₃	m ₄
33 1.30	B 8 B 10 B 12 B 14				4.5 0.18	55 2.17	30.5 1.20	14.5 0.57	23.5 0.93	22 0.87	20 0.79	21 0.83	23.5 0.93	20 0.79

Specification

- Body
Zinc die-cast
Powder coated
Black, textured finish
- Straight adjustable lever GN 302.1 → page 456
- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish
- Threaded stud
Stainless steel AISI 303
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

Clamping plates GN 9054.6 are used in connection with position indicators EN 9054 / EN 9154. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...

- Digital Position Indicators EN 9054 → page XYZ
- Digital Position Indicators EN 9154 → page XYZ

How to order	¹ Width b
	² Bore d ₁

GN9054.6-33-B12