



Metric table

Dimensions in: millimeters - inches

1 $d_1 -0.1$	2 d_2	3 $h_1 \pm 0.01$	h_2	Length l	A/F
25 0.984	M 8	20 0.7874	10 0.39	20 0.79	22 0.87
25 0.984	M 8	40 1.5748	20 0.79	25 0.98	22 0.87
40 1.575	M 12	35 1.3780	20 0.79	30 1.18	36 1.42
40 1.575	M 12	70 2.7559	20 0.79	35 1.38	36 1.42

Specification

- Body
Steel
- Case-hardened
- Blackened finish
- Set screw DIN 913
Steel, blackened finish
- RoHS compliant

Information

Height adjusting cylinders GN 9192.3 are used to increase the clamping height of down-thrust clamps GN 9192.

Height adjusting cylinders can also be used in combination with positioning elements and clamping pads to position contact points at a greater distance from the reference surface.

see also...

- Down-Thrust Clamps GN 9192 → page QVX
- Positioning Ring GN 9192.2 → page QVX
- Clamping Pads GN 709.1 → page QVX
- Clamping Pads GN 709.3 → page QVX
- Positioning and Supporting Elements GN 408.1 → page QVX
- Positioning Elements GN 409.1 → page QVX

How to order	1 Diameter d_1
	2 Thread d_2
	3 Height h_1
GN 9192.3-40-M12-70	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4