



2 Bore code

B Without keyway

4 Type

A Without handle

D With revolving handle

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ H9 Bore	d ₃	d ₆	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
125 4.92	10 .39	55 2.17	32 1.26	18 .71	15 .59	22 .87	28 1.10	65 2.56	47 1.85	23 .91	M 8
160 6.30	10 .39	70 2.76	42 1.65	22 .87	17 .67	26 1.02	35 1.38	65 2.56	60 2.36	23 .91	M 8
200 7.87	12 .47	85 3.35	53 2.09	26 1.02	20 .79	27 1.06	40 1.57	80 3.15	75 2.95	26 1.02	M 10
250 9.84	12 .47	105 4.13	68 2.68	30 1.18	22 .87	30 1.18	49 1.93	80 3.15	99 3.90	26 1.02	M 10

Specification

- Plastic
Duroplast (Phenolic PF)
- High strength reinforced
- Black, shiny finish
- Hub bushing
Steel, blackened finish
- Revolving handles
Plastic, Duroplast
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Other modifications such as inch and special metric bores, keyways, set screw holes, etc.

Information

EN 940 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels EN 950 → page QVX

How to order

EN 940-125-B10-A

1	Handwheel diameter d ₁
2	Bore code
3	Bore diameter d ₂
4	Type