


Mounting example



**3 Type**

- A Without mounting holes
- B With mounting holes for rotary table

**Metric table**

**1**

**2**

Dimensions in: millimeters - inches

b Size of the slide	l <sub>1</sub>	d <sub>1</sub> Socket cap screws DIN 912	d <sub>2</sub> For socket cap screws DIN 912 Type B	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	Type B for rotary table
30 1.18	41 1.61	M 2.5	-	5 0.20	4.2 0.17	35.4 1.39	-
50 1.97	67 2.64	M 3	5.5 0.22	8 0.31	7 0.28	58 2.28	GN 900.6-55
80 3.15	105 4.13	M 4	5.5 0.22	12 0.47	12.5 0.49	92 3.62	GN 900.6-80
120 4.72	145 5.71	M 5	5.5 0.22	16 0.63	13.8 0.54	131.8 5.19	GN 900.6-80

**Specification**

- Body  
Aluminum  
Anodized finish, natural color
- Socket cap screws DIN 912  
Stainless steel
- RoHS compliant

**Information**

GN 900.4 mounting plates of type A are used for mounting components on the operator's side. Type B is used for installing a GN 900.6 rotary table.

The mounting plate can be clamped onto the slide in such a way that no additional mounting holes are required in the slide.

The small fixing plate is used for additional adjustment of the mounting plate on the adjustable slide unit.

All parts required for mounting are included.

see also...

- Adjustable Slide Units GN 900 → page 1942
- Rotary Tables GN 900.6 → www.jwwinco.com

How to order

**GN900.4-50-67-B**

- 1** Width b
- 2** Length l<sub>1</sub>
- 3** Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10