



Metric table

1		2		Dimensions in: millimeters - inches													
b	d ₁ F9 Bore	B 12	B 14	B 15	B 16	B 20	d ₂	l ₁	l ₂	l ₃	l ₄	l ₅	m ₁	m ₂	m ₃	m ₄	m ₅
48							5.5	73	40.5	18	24.5	30	34	36	33.6	25	17
1.89							0.22	2.87	1.59	0.71	0.96	1.18	1.34	1.42	1.32	0.98	0.67

Specification

- Body
Zinc die-cast
Powder coated
Black, textured finish
- Straight adjustable lever GN 302.1 → page 456
- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish
- Threaded stud
Stainless steel AISI 303
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 9053.6 clamping plates are used in connection with EN 9053 and EN 9153 digital position indicators. The mounting holes support typical hole patterns. After installation and adjustment of the spindles, they can easily be clamped and locked. At the same time these plates include bore size Ø 6.1 mm to accept the torque limiter for the position indicator. The clamping plate can be installed so that the adjustable lever is positioned either to the right or the left.

see also...

- Digital Position Indicators EN 9053 → page 378
- Digital Position Indicators EN 9153 → page 382

How to order	1	Width b
GN9053.6-48-B12	2	Bore d ₁