



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ l_1	² d_1 Thread	³ l_2	d_2	h_1	$h_2 \approx$
45 1.77	M 6	20 0.79	10 0.39	9 0.35	34 1.34
63 2.48	M 6	20 0.79	10 0.39	12 0.47	44 1.73

¹ l_1	² d_3 Thread	$h_2 \approx$
63 2.48	M 8	45 1.77
78 3.07	M 8	54 2.13
78 3.07	M 10	54 2.13
92 3.62	M 10	64 2.52

Specification

- Lever body
Stainless steel precision casting AISI CF-8
Matte shot-blasted finish **GS**
- Tapped insert / threaded stud
Stainless steel AISI 303
- Retaining screw
Stainless steel AISI 303
- Spring
Stainless steel AISI 301
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 911.3 adjustable levers replace the DIN 912 socket cap screws or the DIN 917 cap nuts of connector clamps and linear actuator connectors in stainless steel.
The table of dimensions of the connector clamps and linear actuator connectors shows the matching lever for each screw location.

How to order (With tapped insert)	¹ Lever length l_1
GN911.3-63-M8-GS	² Thread d_3
	³ Finish

How to order (With threaded stud)	¹ Lever length l_1
GN911.3-45-M6-20-GS	² Thread d_1
	³ Thread length l_2
	⁴ Finish

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10