



- 3 Type**
- A Semi-spherical tip
 - B Pointed tip

Metric table

Dimensions in: millimeters - inches

1 d ₁ Thread	2 l ₁ Nominal length					d ₂	l ₂	l ₃	r	A/F
M 5	8 0.31	12 0.47	16 0.63	20 0.79	-	3 0.12	1 0.04	0.5 0.02	2.5 0.10	2.5
M 6	12 0.47	16 0.63	20 0.79	25 0.98	-	4 0.16	1.8 0.07	0.8 0.03	3 0.12	3
M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	6 0.24	2.5 0.10	1 0.04	5 0.20	4
M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	8 0.31	3.5 0.14	1.5 0.06	6 0.24	5

Specification

- Body
Steel
- Property class 5.8
- Blackened finish
- Tip
Steel, hardened
- *Strength Values of Screws* → page 2127
- **RoHS compliant**

Information

GN 913.2 set screws with hardened semi-spherical tip (type A) are used in applications where point contact is required. They are a lower cost alternative to GN 605 socket set screws and GN 606 socket head cap screws.

Set screws with hardened pointed tip (type B) provide an alternative tip selection. This type may be used as a locator for a drill for example.

see also...

- *Socket Set Screws GN 605 (with Full Sphere)* → page 1102
- *Set Screws GN 913.3 (with Brass or Plastic Tip)* → page 1099
- *Set Screws GN 913.6 (with Retaining Magnet)* → page 2026

How to order GN913.2-M6-20-B	1 Thread d ₁
	2 Thread length l ₁
	3 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10