



**3 Type**

- F Flat
- L L-shaped

**4 Identification no.**

- 1 With bore for countersunk screws DIN 7991
- 2 With bore without countersunk

**Metric table**

<b>1</b> b	<b>2</b> l <sub>1</sub> Type F	<b>2</b> l <sub>2</sub> Type L	l <sub>3</sub>	m	d	s
20 0.79	40 1.57	20 0.79	10 0.39	20 0.79	5.2 0.20	3 0.12
30 1.18	60 2.36	30 1.18	15 0.59	30 1.18	6.3 0.25	4 0.16
40 1.57	80 3.15	40 1.57	20 0.79	40 1.57	8.3 0.33	5 0.20
45 1.77	90 3.54	45 1.77	22.5 0.89	45 1.77	8.3 0.33	5 0.20

Dimensions in: millimeters - inches

**Specification**

- Sheet steel
- Zinc plated, blue passivated finish **ZB**
- Powder coated
- Black, RAL 9005, textured finish **● SW**
- Silver, RAL 9006, textured finish **● SR**
- RoHS compliant

**Information**

GN 967 connecting brackets are most commonly used in connection with profile systems. Flat or L-shaped can thus be achieved in the smallest of spaces, with a high degree of stability.

In addition to use with profile systems, connecting brackets can also be used for a wide variety of different fixing and retaining tasks, e.g. in fixtures construction.

For identification no. 2, the bores are plain without countersunk to enable mounting with socket cap screws, nuts or rivets.

see also...

- Product Family Standard Parts for Profile Systems → page QVX
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems) → page QVX
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems) → page QVX

How to order (Flat)	<b>1</b> Width b
	<b>2</b> Length l <sub>1</sub>
	<b>3</b> Type
	<b>4</b> Identification no.
	<b>5</b> Finish
<b>GN 967-20-40-F-2-SW</b>	

How to order (L-shaped)	<b>1</b> Width b
	<b>2</b> Length l <sub>2</sub>
	<b>3</b> Type
	<b>4</b> Identification no.
	<b>5</b> Finish
<b>GN 967-30-30-L-1-SW</b>	