








Metric table

d	b	a		h ₁		h ₂	h ₃	Length l	m	Clamping force per clamping jaw	Max. tightening torque in Nm				
		Type GA / Type GL		Type RF											
		min.	max.	min.	max.			max.	Type GA						
M 8	21	39.5	44.5	34.5	39.5	15	4.5	7.5	15	10	25				
	0.83	1.56	1.75	1.36	1.56	0.59	0.18	0.30	0.59	0.39	3372 lbf				
M 8	25	39.5	44.5	34.5	39.5	15	4.5	7.5	15	12	25				
	0.98	1.56	1.75	1.36	1.56	0.59	0.18	0.30	0.59	0.47	3372 lbf				
M 8	32	39.5	44.5	34.5	39.5	15	4.5	7.5	15	16	25				
	1.26	1.56	1.75	1.36	1.56	0.59	0.18	0.30	0.59	0.63	3372 lbf				
M 8	40	39.5	44.5	34.5	39.5	15	4.5	7.5							

Type **GL** smooth clamping surfaces (jaw blank for workpiece-specific clamping contours)



Type **GA** with 2 fixing threads for attachment jaws



Type **RF** ribbed clamping surfaces

