



5 Type

- A Without bores
- C With bores and slotted holes

Metric table

Dimensions in: millimeters - inches

h ₁		b ₁	l ₁	b ₃	d	h ₂	l ₂	m ₁	m ₂	s
ALM	STB									
30	30	45	30	18	6.2	18	15	-	20	4
1.18	1.18	1.77	1.18	0.71	0.24	0.71	0.59		0.79	0.16
30	30	45	60	18	6.2	18	15	30	20	4
1.18	1.18	1.77	2.36	0.71	0.24	0.71	0.59	1.18	0.79	0.16
40	40	60	40	24	8.2	24	20	-	25	5
1.57	1.57	2.36	1.57	0.94	0.32	0.94	0.79		0.98	0.20
40	40	60	80	24	8.2	24	20	40	25	5
1.57	1.57	2.36	3.15	0.94	0.32	0.94	0.79	1.57	0.98	0.20
50	-	75	50	30	10.2	30	25	-	30	6
1.97		2.95	1.97	1.18	0.40	1.18	0.98		1.18	0.24
50	-	75	100	30	10.2	30	25	50	30	6
1.97		2.95	3.94	1.18	0.40	1.18	0.98	1.97	1.18	0.24

Specification

- Structural steel
Drawn, with sharp edges
Blackened finish
- Aluminum
Pressed
Matte, tumbled finish
- RoHS compliant



STB

ALM

Information

GN 970 connecting brackets are used universally for right-angle connecting and mounting of e.g. base plates or covers.

Type A allows for the use of hole patterns specific to the application as well as mounting by welding.

Type C connecting brackets have one or two combinations of a bore and a slotted hole depending on the length l₁.

see also...

- Connecting Brackets GN 967 → www.jwwinco.com

How to order	
1	Material
2	Height h ₁
3	Width b ₁
4	Length l ₁
5	Type

GN970-STB-40-60-80-B

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10