



2 Bore code

B Without keyway

4 Type

A Without handle

R With revolving handle

Specification



- Aluminum die-cast
 - Contact face of hub machined
 - Rim turned
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
- Radial and axial runout of the rim < 0.4 mm
- Stepped cylindrical revolving handle GN 798.2 → www.jwwinco.com
 - Plastic Technopolymer
 - Black, matte finish
 - Threaded spindle
 - Steel, zinc plated, blue passivated finish
- Keyways *WN / DIN 6885* → page 2039 / 2040
- Cross Holes *GN 110* → page 2042
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Accessory

- Countersunk washers GN 184 → page 1150

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc.

Information

GN 924 flat-faced spoked handwheels are distinguished by their modern design.

The removable plastic cover shrouds the mounting components such as screws, countersunk washers as well as the shaft end.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Two Spoked Handwheels *GN 322 (Aluminum, Rim Highly Polished)* → page 214

How to order (Inch)	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type
	5 Color
<p>GN 924-140-B5/8-A-SW</p>	

How to order (Metric)	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type
	5 Color
<p>GN 924-200-B18-R-SR</p>	

Inch table

Dimensions in: inches - *millimeters*

¹ d₁	³ d₂ +0.001 Bore	d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	∅ Handle GN 798.2	Recommended countersunk washer
4.92 125	1/2	1.22 31	0.91 23	0.59 15	0.43 11	0.71 18	1.32 33.5	2.42 61.5	1.79 45.5	0.87 22	184-20
5.51 140	5/8	1.42 36	1.12 28.5	0.65 16.5	0.51 13	0.75 19	1.44 36.5	3.01 76.5	2.05 52	0.94 24	184-25
6.30 160	5/8	1.42 36	1.12 28.5	0.71 18	0.57 14.5	0.79 20	1.56 39.5	3.01 76.5	2.40 61	0.94 24	184-25
7.87 200	3/4	1.65 42	1.42 36	0.81 20.5	0.63 16	0.94 24	1.79 45.5	3.35 85	3.05 77.5	0.98 25	184-32

Metric table

Dimensions in: millimeters - *inches*

¹ d₁	³ d₂ H7 Bore		d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	∅ Handle GN 798.2	Recommended countersunk washer
125 4.92	12	14	31 1.22	23 0.91	15 0.59	11 0.43	18 0.71	33.5 1.32	61.5 2.42	45.5 1.79	22 0.87	184-20
140 5.51	14	16	36 1.42	28.5 1.12	16.5 0.65	13 0.51	19 0.75	36.5 1.44	76.5 3.01	52 2.05	24 0.94	184-25
160 6.30	14	16	36 1.42	28.5 1.12	18 0.71	14.5 0.57	20 0.79	39.5 1.56	76.5 3.01	61 2.40	24 0.94	184-25
200 7.87	18	20	42 1.65	36 1.42	20.5 0.81	16 0.63	24 0.94	45.5 1.79	85 3.35	77.5 3.05	25 0.98	184-32

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

