



**Specification**



- Plastic  
Technopolymer (Polyethylene PE)
  - Black, RAL 9005, matte finish
  - Gray, RAL 7042, matte finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

- SW**
- GR**

**On request**

- Additional sizes
- White, RAL 9003, matte finish

- WS**

**Information**

EN 991 tube end plugs have been designed for sealing tube ends for safety or visual reasons. They are pressed into the tube end either by hand or with a mallet.

see also...

- *Threaded Tube Ends GN 992 (Aluminum)* → page 1581
- *Threaded Tube Ends GN 992.5 (Stainless Steel)* → page 1581

How to order	
<b>1</b>	Length $s_1$
<b>2</b>	Width $s_2$
<b>3</b>	Color
<b>EN 991-R25-20-SW</b>	

**Metric table**

<sup>1</sup> S <sub>1</sub>	<sup>2</sup> S <sub>2</sub>	w	l <sub>1</sub>	l <sub>2</sub>	<sup>1</sup> S <sub>1</sub>	<sup>2</sup> S <sub>2</sub>	w	l <sub>1</sub>	l <sub>2</sub>
R 20	10 0.39	0.8 ... 2	3 0.12	12 0.47	R 50	25 0.98	1 ... 3	5 0.20	11.5 0.45
R 20	15 0.59	1 ... 2	5 0.20	11.5 0.45	R 50	30 1.18	1 ... 3	5 0.20	12 0.47
R 25	10 0.39	0.8 ... 2	3 0.12	11.5 0.45	R 50	35 1.38	1 ... 3.5	5 0.20	14.5 0.57
R 25	15 0.59	1 ... 2.5	5 0.20	11.5 0.45	R 50	40 1.57	1.5 ... 3	5 0.20	15 0.59
R 25	20 0.79	1 ... 3	5 0.20	11.5 0.45	R 60	20 0.79	1 ... 3	5 0.20	14.5 0.57
R 30	10 0.39	1 ... 2	5 0.20	11.5 0.45	R 60	30 1.18	1 ... 2.5	5 0.20	15 0.59
R 30	15 0.59	1 ... 2.5	5 0.20	11.5 0.45	R 60	40 1.57	1 ... 3	5 0.20	14 0.55
R 30	20 0.79	1 ... 3	5 0.20	11.5 0.45	R 60	50 1.97	1.5 ... 3.5	5 0.20	14.5 0.57
R 35	20 0.79	1 ... 2.5	5 0.20	11.5 0.45	R 70	30 1.18	1 ... 3	5 0.20	15 0.59
R 35	25 0.98	1 ... 3	5 0.20	11.5 0.45	R 70	40 1.57	1.5 ... 3	5 0.20	20 0.79
R 40	15 0.59	1 ... 2	5 0.20	12 0.47	R 80	20 0.79	1 ... 3	5 0.20	18 0.71
R 40	20 0.79	1 ... 3	5 0.20	12 0.47	R 80	30 1.18	1 ... 2.5	5 0.20	14.5 0.57
R 40	25 0.98	1 ... 3	5 0.20	11.5 0.45	R 80	40 1.57	1 ... 3	5 0.20	14.5 0.57
R 40	30 1.18	1 ... 3	5 0.20	11 0.43	R 80	50 1.97	1.5 ... 4	5 0.20	22 0.87
R 45	15 0.59	1.5 ... 2	5 0.20	11 0.43	R 80	60 2.36	1.5 ... 3.5	5 0.20	25 0.98
R 45	20 0.79	1 ... 3	5 0.20	11.5 0.45	R 100	40 1.57	1.5 ... 4	5 0.20	14.5 0.57
R 45	25 0.98	1 ... 3	5 0.20	12 0.47	R 100	50 1.97	1.5 ... 4.5	5 0.20	24 0.94
R 50	20 0.79	1 ... 3	5 0.20	15 0.59					

Dimensions in: millimeters - inches

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

