



SS Stainless Steel

Metric table

1		2		Dimensions in: millimeters - inches							
b	d ₁			d ₂	l ₁	l ₂	l ₃	l ₄	m ₁	m ₂	
24 0.94	B 6	B 8	B 10	3.2 0.13	38 1.50	28 1.10	8 0.31	29.5 1.16	15 0.59	18 0.71	

Specification

- Body
Plastic
Technopolymer (Polyamide PA-HP)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Adjustable lever
- Plastic
Technopolymer (Polyamide PA)
Glass fiber reinforced
Black, matte finish
- Tapped insert
Stainless steel AISI 304
- Hex head screw
Stainless steel AISI 316
- *Stainless Steel Characteristics* → page QVX
- RoHS

Information

Clamping plates EN 955.6 are used in connection with digital position indicators EN 955 / EN 955.2. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1mm to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the adjustable lever is situated as required either on the right or the left.

see also...

- *Digital Position Indicators EN 955 (Steel Shaft Receptacle)* → page QVX
- *Digital Position Indicators EN 955.2 (Stainless Steel Shaft Receptacle)* → page QVX

How to order	1	Width b
	2	Bore d ₁
EN955.6-24-B6		

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4