



3 Type

- D With plain spindle
- E With threaded spindle

Metric table

2

Dimensions in: millimeters - inches

d ₁	d ₂ h8 Type D		d ₃ Type E		d ₄ h13	l ₁ ≈	l ₂	l ₃	A/F Internal hex
	ST / AL	KT	ST / AL	KT					
16 0.63	7 0.28	7 0.28	M 6	M 6	10 0.39	49 1.93	11 0.43	5.5 0.22	3
20 0.79	8 0.31	8 0.31	M 8	M 8	13 0.51	61 2.40	13 0.51	6 0.24	4
25 0.98	10 0.39	10 0.39	M 10	M 10	16 0.63	75 2.95	14 0.55	8 0.31	5
32 1.26	13 0.51	13 0.51	M 12	M 12	20 0.79	95 3.74	21 0.83	10.5 0.41	6
36 1.42	16 0.63	-	M 16	-	22 0.87	106 4.17	26 1.02	11 0.43	8

Specification

1

- Steel, zinc plated, blue passivated finish **ST**
- Aluminum **AL**
Turned and polished
- Plastic **KT**
Technopolymer (Polyamide PA)
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Spindle
Steel, zinc plated, blue passivated finish
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- RoHS compliant

Information

DIN 98 revolving handles have a comfortable grip and are widely used on crank handles or handwheels. Type D handles are supplied unassembled so that the spindle can be press-fit or screwed into a tapped blind bore prior to assembly. During mounting, easy blows with a soft mallet are sufficient to drive the handle into place.

How to order DIN98-KT-20-E	1	Material
	2	Handle diameter d ₁
	3	Type