



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Bore	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	l ₁	l ₂	k	s
46 1.81	B 8	22 0.87	22 0.87	6 0.24	25 0.98	22 0.87	53 2.09	108 4.25	28 1.10	32 1.26	7 0.28
56 2.20	B 10	26 1.02	28 1.10	8 0.31	30 1.18	27 1.06	60 2.36	127 5.00	34 1.34	39 1.54	9 0.35

Specification

- Body
Nylon plastic
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Hub
Steel, zinc plated, molded-in
- Arm
Steel, zinc plated
- Cover disk
Aluminum, matte anodized finish, self-adhesive
- Hand piece
Phenolic plastic
- Temperature resistant up to 300 °F (150 °C)
- Black
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special metric and inch size bores, threads, keyways, etc.

Information

The unique shape of these LM economical control levers is suited to be used for most any control applications.

The disk cover hides fasteners and provides an area for printing of symbols or logos. After assembly, the self-adhesive disk cover is pressed in by hand.

<p>How to order</p> <p>¹ ²</p> <p>LM-46-B8</p>	1	Diameter d ₁
	2	Bore d ₂