



Specification

- Plastic
Technopolymer (Polyethylene PE)
- Black, RAL 9005, matte finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**



- **SW**
- **GR**

On request

- Additional sizes
- White, RAL 9003, matte finish

- **WS**

Information

EN 991 tube end plugs have been designed for sealing tube ends for safety or visual reasons. They are pressed into the tube end either by hand or with a mallet.

see also...

- *Construction Tubes GN 990* → page 1836
- *Rods / Tubes GN 480.1* → page 1838
- *Threaded Tube Ends GN 992 (Aluminum)* → page 1581
- *Threaded Tube Ends GN 992.5 (Stainless Steel)* → page 1581

How to order

EN991-D10-SW

- 1 Diameter d (Square s)
- 2 Color

Metric table

Dimensions in: millimeters - inches

d ∅	w	l₁	l₂	For round tube	d ∅	w	l₁	l₂	For round tube
D 10	1 ... 2	3.5 <i>0.14</i>	11 <i>0.43</i>	GN 990	D 35	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
D 12	1 ... 2	3.5 <i>0.14</i>	11 <i>0.43</i>	GN 990	D 36	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	-
D 13	1 ... 2	4 <i>0.16</i>	11 <i>0.43</i>	1/4"	D 38	1 ... 3.5	5 <i>0.20</i>	11.5 <i>0.45</i>	-
D 14	1 ... 2	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	D 40	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
D 15	1 ... 2	3 <i>0.12</i>	11.5 <i>0.45</i>	GN 990	D 42	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
D 16	1 ... 2	5 <i>0.20</i>	11 <i>0.43</i>	GN 990	D 45	1 ... 3	5 <i>0.20</i>	11 <i>0.43</i>	GN 990
D 18	1 ... 2	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	D 48	1.2 ... 3.6	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
D 20	1 ... 2.5	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	D 50	2.5 ... 4.5	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
D 22	1 ... 2	5 <i>0.20</i>	11.5 <i>0.45</i>	-	D 55	3 ... 5	5 <i>0.20</i>	14.5 <i>0.57</i>	GN 990
D 25	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	D 60	3 ... 5	5 <i>0.20</i>	17.5 <i>0.69</i>	GN 990
D 26	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	-	D 70	1.5 ... 3.5	5 <i>0.20</i>	21 <i>0.83</i>	-
D 27	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	3/4"	D 76	1.6 ... 4	6 <i>0.24</i>	21.5 <i>0.85</i>	2 1/2"
D 28	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	-	D 80	1.5 ... 3	5 <i>0.20</i>	22 <i>0.87</i>	-
D 30	1 ... 2.5	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	D 88	1.5 ... 4	6 <i>0.24</i>	21.5 <i>0.85</i>	3"
D 32	1 ... 3	5 <i>0.20</i>	12 <i>0.47</i>	GN 990	D 90	1.5 ... 5	6 <i>0.24</i>	21 <i>0.83</i>	-
D 34	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	1"	D 100	2 ... 4.5	6 <i>0.24</i>	28.5 <i>1.12</i>	-

s □	w	l₁	l₂	For square tube	s □	w	l₁	l₂	For square tube
V 10	0.8 ... 2.5	4 <i>0.16</i>	12 <i>0.47</i>	GN 990	V 35	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990
V 12	1 ... 2	4 <i>0.16</i>	12 <i>0.47</i>	GN 990	V 40	1 ... 3	5 <i>0.20</i>	14.5 <i>0.57</i>	GN 990
V 15	1 ... 2	3 <i>0.12</i>	11.5 <i>0.45</i>	-	V 45	1 ... 3	5 <i>0.20</i>	14.5 <i>0.57</i>	GN 990
V 16	1 ... 2.5	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	V 50	2.6 ... 4	5 <i>0.20</i>	24 <i>0.94</i>	GN 990
V 18	1.5 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	-	V 55	2 ... 4.5	5.5 <i>0.22</i>	14.5 <i>0.57</i>	-
V 20	1 ... 2	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	V 60	1.5 ... 3.5	5 <i>0.20</i>	15 <i>0.59</i>	-
V 22	1 ... 3.5	5 <i>0.20</i>	12 <i>0.47</i>	-	V 70	2 ... 5	5 <i>0.20</i>	22 <i>0.87</i>	-
V 25	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	V 80	1.5 ... 4	6 <i>0.24</i>	21 <i>0.83</i>	-
V 30	1 ... 3	5 <i>0.20</i>	11.5 <i>0.45</i>	GN 990	V 90	3 ... 5	6 <i>0.24</i>	21 <i>0.83</i>	-
V 34	1 ... 3	5 <i>0.20</i>	14.5 <i>0.57</i>	-	V 100	1 ... 4	7 <i>0.28</i>	21 <i>0.83</i>	-

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

