



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

1			2				
d ₁			d ₂	d ₃	h ₁	h ₂ ≈	Length l ≈
GN 99.7	GN 99.8 AISI 304	GN 99.8 AISI 316L					
16 0.63	16 0.63	16 0.63	M 8	10 0.39	12.5 0.49	26 1.02	47.5 1.87
20 0.79	20 0.79	20 0.79	M 10	12 0.47	15 0.59	32 1.26	59.5 2.34
25 0.98	25 0.98	25 0.98	M 12	14 0.55	19 0.75	40 1.57	75.5 2.97
32 1.26	32 1.26	-	M 16	18 0.71	25 0.98	52 2.05	94.5 3.72
40 1.57	40 1.57	-	M 20	20 0.79	31 1.22	62 2.44	118 4.65

Specification

- **GN 99.7**
Steel, zinc plated, blue passivated finish —
- **GN 99.8**
Stainless steel, matte shot-blasted finish
- AISI 304 —
- AISI 316L **A4**
- Clamp arms
Butt-welded to tapped hub
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

Information

Latest production techniques make these GN 99.7 and GN 99.8 double arm clamp nuts an extremely good value.

see also...

- *Double Arm Clamp Nuts GN 206.1 (Malleable Iron)* → page 546
- *Double Arm Clamp Nuts GN 206.1 (Stainless Steel)* → page 546

On request

- Special inch and metric bores or threads

How to order (Steel) 1 2 GN 99.7-20-M10	1 Diameter d ₁
	2 Thread d ₂
How to order (Stainless steel AISI 304) 1 2 GN 99.8-32-M16	1 Diameter d ₁
	2 Thread d ₂
How to order (Stainless steel AISI 316L) 1 2 3 GN 99.8-25-M12-A4	1 Diameter d ₁
	2 Thread d ₂
	3 Material

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4