



**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	b <sub>1</sub>	b <sub>2</sub>	s	t	Suitable for bearing lock nut
10 0.39	21 0.83	13.5 0.53	3 0.12	3 0.12	1 0.04	8.5 0.33	KM-M10X0.75
12 0.47	25 0.98	17 0.67	3 0.12	3 0.12	1 0.04	10.5 0.41	KM-M12X1
15 0.59	28 1.10	21 0.83	4 0.16	4 0.16	1 0.04	13.5 0.53	KM-M15X1
17 0.67	32 1.26	24 0.94	4 0.16	4 0.16	1 0.04	15.5 0.61	KM-M17X1
20 0.79	36 1.42	26 1.02	4 0.16	4 0.16	1 0.04	18.5 0.73	KM-M20X1
25 0.98	42 1.65	32 1.26	5 0.20	5 0.20	1.25 0.05	23 0.91	KM-M25X1.5
30 1.18	49 1.93	38 1.50	5 0.20	5 0.20	1.25 0.05	27.5 1.08	KM-M30X1.5
35 1.38	57 2.24	44 1.73	6 0.24	5 0.20	1.25 0.05	32.5 1.28	KM-M35X1.5
40 1.57	62 2.44	50 1.97	6 0.24	6 0.24	1.25 0.05	37.5 1.48	KM-M40X1.5
45 1.77	69 2.72	56 2.20	6 0.24	6 0.24	1.25 0.05	42.5 1.67	KM-M45X1.5
50 1.97	74 2.91	61 2.40	6 0.24	6 0.24	1.25 0.05	47.5 1.87	KM-M50X1.5

**Specification**

- Spring steel, plain finish
- RoHS compliant

**On request**

- Additional sizes

**Information**

MB bearing lock washers according to DIN 5406 are mainly utilized with KM (DIN 981) bearing lock nuts to secure bearings onto a shaft.

see also...

- Bearing Lock Nuts KM → page 1136

**How to order**

**MB-10**

1 Diameter d<sub>1</sub>

