Quick Release Hand Knobs

Aluminum, with Tapped Through Bore





Application example





Inch

Inch table

Dimensions in: inches / millimeters

1 d_1	2 d_2	d_3	h_1	h_2
1.00 25.4	1/4 x 20	0.50 12.7	0.88 22.4	0.50 12.7
1.50 38.1	5/16 x 18	0.63 16	0.88 22.4	0.38 9.7
2.00 50.8	3/8 x 16	0.81 20.6	1.00 25.4	0.50 12.7
2.50 63.5	1/2 x 13	1.00 25.4	1.13 28.7	0.56 14.2

Specification

Aluminum
Solid extrusion 6063-T5
Etched and clear anodized finish

RoHS

On request

- Metric sizes

Quick release hand knobs CKSQ are used in such applications where the knob has to be completely removed after the releasing operation and mounted again rapidly for re-clamping.
The knob is tilted over the threaded spindle. When in position, the knob is brought into a straight position for mating of the two threads on the insert and spindle. The knob will then have to be turned only by a fraction of a rotation to achieve clamping.
Lightweight yet a good choice for medium-duty clamping applications.

see also...	Page
CKS Hand Knobs (with Tapped or Plain Bore, or Blank Type)	QVX

How to order

CKSQ-2.00-3/8X16

1	**Handle diameter d_1**
2	**Thread d_2**

⚠ **WARNING**: Cancer and Reproductive Harm — www.P65Warnings.ca.gov