



Metric table

Dimensions in: millimeters - inches

¹ d_1	² d_2 Thread		d_3	l_1	l_2
17 0.67	M 6	M 8	12 0.47	45 1.77	8 0.31
21 0.83	M 8	M 10	16 0.63	56 2.20	10 0.39
23 0.91	M 8	M 10	16 0.63	61 2.40	10 0.39
25 0.98	M 8	M 10	18 0.71	71 2.80	13 0.51
28 1.10	M 10	M 12	20 0.79	92 3.62	13 0.51
29 1.14	M 10	M 12	20 0.79	122 4.80	13 0.51

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 266 °F (130 °C)
- Black, shiny finish
- Threaded spindle
Steel
- Zinc plated
- With wrench flats
- *Plastic Characteristics* → page 2135
- RoHS compliant

Information

MCG cylindrical revolving handles can be used on most any device where a leverage for turning is required, i.e. handwheels or crank handles.

see also...

- *Retractable Handles MGR (Phenolic Plastic)* → page 51
- *Retractable Handles PGR (Nylon Plastic)* → page 52

<p>How to order</p> <p>¹ ²</p> <p>MCG-17-M6</p>	1	Handle diameter d_1
	2	Thread d_2