



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$	<sup>3</sup> Length $l$		$d_4$	$h_1$	$h_2$
1.50 38.1	1/4 x 20	1.75 44.5	3.00 76.2	0.63 16.0	0.88 22.4	0.38 9.7
2.00 50.8	5/16 x 18	1.75 44.5	3.00 76.2	0.81 20.6	1.00 25.4	0.50 12.7
2.50 63.5	3/8 x 16	1.75 44.5	3.00 76.2	1.00 25.4	1.13 28.7	0.56 14.2
2.50 63.5	1/2 x 13	1.75 44.5	3.00 76.2	1.00 25.4	1.13 28.7	0.56 14.2
3.00 76.2	5/8 x 11	1.75 44.5	3.00 76.2	1.25 31.8	1.25 31.8	0.63 16.0

**Specification**

- Hand knob  
Solid aluminum extrusion 6063-T5, etched and clear anodized finish
- Threaded stud  
Steel, black oxide finish
- Cross Holes GN 110 → page 2042
- RoHS compliant

**On request**

- Cross holes and set screw holes

**Information**

Lightweight yet long-lasting, these CKS hand knobs made from a durable aluminum extrusion are an economical choice for a variety of equipment applications.

see also...

- Hand Knobs CKS (with Tapped or Plain Bore, or Blank Type) → page 636

How to order	<sup>1</sup> Handle diameter $d_1$
<sup>2</sup> <b>CKS-2.50-3/8X16-1.75</b>	<sup>2</sup> Thread $d_2$
<sup>3</sup>	<sup>3</sup> Length $l$

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4