



Universal



Universal table

Dimensions in: millimeters / inches

¹ l ₁	² d ₁ Pilot hole	l ₂	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	d ₅ Ø Handle	d ₆
65 2.56	P 4	87 3.43	18 0.71	16 0.63	27 1.06	33 1.30	30 1.18	10 0.39	50 1.97	21 0.83	M 6
80 3.15	P 4	105 4.13	22 0.87	19 0.75	30 1.18	36 1.42	32 1.26	10 0.39	50 1.97	21 0.83	M 6
100 3.94	P 4	128 5.04	24 0.94	22 0.87	34 1.34	40 1.57	37 1.46	10 0.39	70 2.76	23 0.91	M 8
130 5.12	P 6	162 6.38	28 1.10	25 0.98	40 1.57	49 1.93	44 1.73	14 0.55	90 3.54	26 1.02	M 8
160 6.30	P 6	196 7.72	34 1.34	28 1.10	45 1.77	55 2.17	49 1.93	15 0.59	90 3.54	26 1.02	M 10

Specification

Crank body

- Nylon plastic
- Glass fiber reinforced
- Operating temperature up to 230 °F (110 °C)
- Black, matte finish

Hub bushing

Steel, zinc plated

Revolving handle

- Nylon plastic
- Black, matte finish
- Threaded spindle
- Steel, zinc plated

RoHS

On request

- Other modifications such as inch and metric bores, squares, keyways, set screw holes, etc.

Crank handles MH-MEP are of modern design and are suitable for light duty applications.

see also...

	Page
MH-MRS Crank Handles	QVX
MH-PGR Crank Handles	QVX
MV-M Crank Handles	QVX

Technical Information

Keyways WN 6885 / DIN 6885-1	QVX
Plastic Characteristics	QVX

How to order

MH-MEP-65-P4

- ¹ Length l₁
- ² Pilot hole d₁