



Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² d ₂ | ³ Length l | | | | b | h |
|-----------------------------|-----------------------------|-----------------------|------------|------------|------------|------------|------------|
| 22 0.87 | M 4 | 10 0.39 | - | - | - | 9 0.35 | 10 0.39 |
| 22 0.87 | M 5 | 10 0.39 | 15 0.59 | - | - | 9 0.35 | 10 0.39 |
| 26 1.02 | M 5 | 10 0.39 | 15 0.59 | - | - | 11 0.43 | 11 0.43 |
| 26 1.02 | M 6 | 10 0.39 | 15 0.59 | 20 0.79 | 25 0.98 | 11 0.43 | 11 0.43 |
| 32 1.26 | M 6 | 10 0.39 | 15 0.59 | 20 0.79 | 25 0.98 | 12 0.47 | 12 0.47 |

Specification

- Wing body
Nylon plastic
- Glass filled
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Threaded stud
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- For certain minimum quantities, custom colors or special studs

Information

Due to their low height GS wing screws offer a comfortable grip for quick two finger clamping applications.

see also...

- *Wing Screws GP (with Protruding Hub)* → page 671

| | |
|--|---|
| How to order | ¹ Handle diameter d ₁ |
| ¹ ² ³ GS-22-M5-15 | ² Thread d ₂ |
| | ³ Length l |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4