



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Bore	l ₂	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	d ₅ Ø Handle	d ₆
80 3.15	B 7.9	105 4.13	22 0.87	19 0.75	30 1.18	25 0.98	29 1.14	3 0.12	50 1.97	21 0.83	M 6

Specification

- Crank body
Nylon plastic
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Hub bushing
Stainless steel
- Revolving handle
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Threaded spindle
Stainless steel AISI 303
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and special metric bores, squares, keyways, set screw holes, etc.

Information

MV-PM crank handles are of modern design and are suitable for light duty applications.

<p>How to order</p> <p>¹ ²</p> <p>MV-PM-80-B7.9</p>	1	Length l ₁
	2	Bore d ₁

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4