



SS Stainless Steel

4 Type

- A Without pad
- B With light duty pad
- D With heavy duty pad

Inch table

d ₁		-	d ₂ Thread		l ₁				l ₂	l ₃	l ₄		A/F	Max. load	
			Light duty pad	Heavy duty pad	Light duty pad	Without pad / heavy duty pad									
2.00 50.8	2.50 63.5	-	3/8 x 16	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	3/4	1500 lbf 6672.33 N	2000 lbf 8896.44 N	
2.00 50.8	2.50 63.5	-	1/2 x 13	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	3/4	3000 lbf 13344.66 N	3500 lbf 15568.77 N	
3.00 76.2	4.00 101.6	-	1/2 x 13	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	3/4	3000 lbf 13344.66 N	3500 lbf 15568.77 N	
2.00 50.8	2.50 63.5	-	5/8 x 11	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	7/8	4500 lbf 20016.99 N	5000 lbf 22241.10 N	
3.00 76.2	4.00 101.6	6.00 152.4	5/8 x 11	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	7/8	4500 lbf 20016.99 N	5000 lbf 22241.10 N	
3.00 76.2	4.00 101.6	6.00 152.4	3/4 x 10	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	11/16	5500 lbf 24465.21 N	6000 lbf 26689.32 N	

Dimensions in: inches - millimeters

Specification

- **LP 100**
Base / threaded stud / hex nuts
Steel, zinc plated, blue passivated finish
- **LP 100.1**
Base / threaded stud / hex nuts
Stainless steel AISI 303
- Vibration damping pad
Rubber, waffle-style
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

On request

- Metric sizes

Information

LP 100 and LP 100.1 anti-vibration leveling mounts are for medium to heavy duty applications. These durable mounts are utilized where a lower base height is required.

A coupling nut is not recommended to use for installation. Use a nut or tapped hole of 1 - 1 1/2 times the thread diameter of the threaded stud.

To insure a proper leveling mount size, divide the machine weight by the number of mounts required. This will equal the pounds or load per mount.

Two hex nuts are included with each leveling mount.

see also...

- "Anti-Vibe®" Anti-Vibration Leveling Mounts AVM (Inch Thread, Steel) → page 1562
- Vibration Damping Leveling Feet GN 342.2 (Metric Thread, Steel) → www.jwwinco.com

How to order (Steel)	1 Base diameter d ₁
1 2 3 4	2 Thread d ₂
LP100-2.50-1/2X13-4.00-B	3 Stud length l ₁
	4 Type
How to order (Stainless steel)	1 Base diameter d ₁
1 2 3 4	2 Thread d ₂
LP100.1-4.00-5/8X11-3.00-A	3 Stud length l ₁
	4 Type