



Metric table

Dimensions in: millimeters - inches

T-slot width	¹ d	² a	e ₁	e ₂	h	k
6 0.24	M 5	5.7 0.22	20 0.79	10 0.39	8 0.31	4 0.16
8 0.31	M 6	7.7 0.30	26 1.02	13 0.51	10 0.39	6 0.24
10 0.39	M 8	9.7 0.38	30 1.18	15 0.59	12 0.47	6 0.24
12 0.47	M 10	11.7 0.46	36 1.42	18 0.71	14 0.55	7 0.28
14 0.55	M 12	13.7 0.54	44 1.73	22 0.87	16 0.63	8 0.31
16 0.63	M 14	15.7 0.62	50 1.97	25 0.98	18 0.71	9 0.35
18 0.71	M 16	17.7 0.70	56 2.20	28 1.10	20 0.79	10 0.39
20 0.79	M 18	19.7 0.78	64 2.52	32 1.26	24 0.94	12 0.47
22 0.87	M 20	21.7 0.85	70 2.76	35 1.38	28 1.10	14 0.55
28 1.10	M 24	27.7 1.09	88 3.46	44 1.73	36 1.42	18 0.71
36 1.42	M 30	35.6 1.40	108 4.25	54 2.13	44 1.73	22 0.87

Specification

- Steel
 - Property class 10
 - Tempered
- *Strength Values of Nuts* → page 2127
- RoHS compliant

Information

NO.508L extended T-slot nuts are used on precision machines to protect T-slots.

How to order ¹ ² NO.508L-20-M18	1 T-slot width
	2 Thread d