



- 4 Type**
- C1** Steel base, yellow zinc plated
  - C2** Steel base, black oxide finish
  - C3** Solid Delrin® plastic base
  - C4** Molded Delrin® plastic base

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	A/F	Max. load	
						Steel base	Delrin® plastic base
19.1 0.75	M 6	25.4 1.00	13.5 0.53	2.5 0.100	9.5 0.375	3113.75 N 700 lbf	667.23 N 150 lbf
25.4 1.00	M 8	31.8 1.25	17.8 0.70	3.6 0.141	12.7 0.500	4448.22 N 1000 lbf	889.64 N 200 lbf
31.8 1.25	M 10	50.8 2.00	22.4 0.88	4.3 0.170	15.9 0.625	16680.83 N 3750 lbf	1334.46 N 300 lbf
47.8 1.88	M 12	50.8 2.00	28.7 1.13	6.4 0.250	19.1 0.750	22241.10 N 5000 lbf	3113.75 N 700 lbf
63.5 2.50	M 16	50.8 2.00	31.8 1.25	8.9 0.350	22.2 0.875	26689.32 N 6000 lbf	5337.86 N 1200 lbf
76.2 3.00	M 20	50.8 2.00	38.1 1.50	10.4 0.410	27.0 1.062	32916.84 N 7400 lbf	8006.79 N 1800 lbf
101.6 4.00	M 24	88.9 3.50	47.8 1.88	11.2 0.440	34.9 1.375	88964.43 N 20000 lbf	10675.73 N 2400 lbf
101.6 4.00	M 24	108.0 4.25	47.8 1.88	11.2 0.440	34.9 1.375	88964.43 N 20000 lbf	10675.73 N 2400 lbf
152.4 6.00	M 30	101.6 4.00	69.9 2.75	19.1 0.750	47.6 1.875	191273.53 N 43000 lbf	16013.59 N 3600 lbf
152.4 6.00	M 30	152.4 6.00	69.9 2.75	19.1 0.750	47.6 1.875	191273.53 N 43000 lbf	16013.59 N 3600 lbf

**Specification**

- **Type C1 / C2**
  - Base  
Steel, yellow zinc plated or black oxide finish
  - Threaded stud with ball end  
Steel, hardened  
Machined from solid bar
- **Type C3 / C4**
  - Base  
Delrin® plastic  
Temperature resistant up to 180 °F (82 °C)
  - Threaded stud with ball end  
Steel, hardened, yellow zinc plated  
Machined from solid bar
- **Jam nut**  
Materials and finishes are the same as the corresponding stud
- **Plastic Characteristics** → page 2135
- **RoHS compliant**

**Information**

MLPST “Level-It”™ leveling mounts swivel 10-15° to all sides of the centerline to adjust to uneven surfaces. They are typically used for leveling machine tools, electronic racks, benches, etc. The large diameter base design assures a solid support.

A coupling nut is not recommended to use for installation. Use a nut or tapped hole of 1 - 1 1/2 times the thread diameter of the threaded stud.

To insure a proper leveling mount size, divide the machine weight by the number of mounts required. This will equal the pounds or load per mount.

The jam nut is a standard part of the assembly.

**On request**

- Non-skid Elastomer pad
- Molded Delrin® plastic base in additional sizes
- For certain minimum quantities, modifications such as mounting holes and other versions of plating

<p><b>How to order</b></p> <p><b>MLPST-1.88-M12-2.00-C1</b></p>	1	Base diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Stud length l <sub>1</sub>
	4	Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

