



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈
21 0.83	M 5	17 0.67	7 0.28	2.5 0.10	57 2.24	7 0.28	8 0.31	54.5 2.15	16.5 0.65	14 0.55	6.3 0.25	4 0.16
23 0.91	M 6	19 0.75	8 0.31	2.5 0.10	77 3.03	7 0.28	8 0.31	84.5 3.33	17.5 0.69	18 0.71	7.5 0.30	4 0.16
26 1.02	M 6	21 0.83	8 0.31	2.5 0.10	97 3.82	7 0.28	10 0.39	96.5 3.80	19 0.75	20 0.79	7.5 0.30	4 0.16

Specification

- Plastic
Nylon
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
 - Revolving
- Retractable mechanism
Steel, zinc plated
- Plastic Characteristics → page QVX
- RoHS compliant

Accessory

- Hex keys ISO 2936 (DIN 911) available for installation → page QVX

On request

- For certain minimum quantities, other handle colors

Information

Suitable for applications in which it is preferred that the revolving handle be folded away when in the rest position, and when a shorter protruding distance of the overall length is required. The handle can be folded in both directions.

see also...

- Retractable Handles PGR (Nylon Plastic) → page QVX
- Retractable Handles MGR (Phenolic Plastic) → page QVX

<p>How to order</p> <p>¹ ²</p> <p>MRS-21-M5</p>	1	Handle diameter d ₁
	2	Thread d ₂