



Metric table

Dimensions in: millimeters - inches

Size	b Slot width	d Ø Housing	h ₁ min.	h ₂ max.	Thread Ø and pitch	Base dimensions length x width	Max. clamping force F
140	18 .71	50 1.97	100 3.94	140 5.51	30 x 6	75 x 110	60 kN 13489 lbf
200	18 .71	50 1.97	140 5.51	200 7.87	30 x 6	75 x 110	60 kN 13489 lbf
320	22 .87	50 1.97	200 7.87	320 12.60	30 x 6	90 x 160	40 kN 8992 lbf
550	22 .87	50 1.97	320 12.60	550 21.65	30 x 6	90 x 160	25 kN 5620 lbf

Specification

- Housing
Cast iron, hammer-effect enameled finish
- Spindle unit
Tempered steel
- Spindle head
Hammer-effect enameled finish
- Centering hole diameter in screw jack head is 12 mm for the No. 6443 pads
- **RoHS compliant**

On request

- NO. 6443 locating pads → page QVX

Information

NO. 6430 atlas screw jacks can be used with DIN 6315B, DIN 6315C and NO. 6315 GN forked clamps. For safety purposes, from slot widths 26 mm and larger, use NO. 6443 locating pads (available upon request).

<p>How to order</p> <p>NO.6430-140-18</p>	1	Size
	2	Width b