

Standard parts in this product family are compatible with aluminum profiles from the i and b modular systems, as well as with common aluminum profile systems from other manufacturers. Using slot nuts or hammerhead screws or nuts, Winco standard elements can be easily and cost-effectively mounted in the groove of the profiles.

- for groove widths 6 (0.24), 8 (0.31) and 10 mm (0.39 inch)
- for grid size 30 (1.18), 40 (1.57) and 45 mm (1.77 inch)



GN 565.1
Cabinet U-Handles
Aluminum,
with Counterbored
Mounting Holes



GN 565.2
Angled Cabinet U-Handles
Aluminum



EN 630.1
**Off-Set
Open U-Handles**
Plastic



EN 528
Cabinet U-Handles
Plastic



GN 728
**Economical
Cabinet U-Handles**
Aluminum Die-Cast



GN 728.5
**Economical
Cabinet U-Handles**
Stainless Steel



EN 628
Bridge Handles
Plastic



EN 629
Cabinet U-Handles
Plastic,
with Cover Cap



EN 629.1
Cabinet U-Handles
Plastic



GN 181
Mounting Plate Sets
Zinc Die-Cast
for Cabinet U-Handles



GN 328
Cabinet U-Handles
Aluminum



GN 328.5
Cabinet U-Handles
Stainless Steel



GN 333.1
Tubular Handles
Aluminum Tube,
with Zinc Die-Cast
Straight Handle Legs



GN 333
Tubular Handles
Aluminum Tube,
with Zinc-Die Cast
Angled Handle Legs



GN 667
Tubular Grip Handles
Aluminum Tube,
Plastic End Pieces



GN 667
Tubular Grip Handles
Stainless Steel Tube,
Plastic End Pieces





**GN 334.1
Oval Tubular Handles**
Aluminum Tube,
Zinc Die-Cast
Handle Legs



**GN 335
Oval Tubular Handles**
Aluminum Tube,
Zinc Die-Cast
Handle Legs



**EN 630
Off-Set Enclosed
Safety U- Handles**
Plastic



**GN 412
Indexing Plungers**
Zinc Die-Cast
with Mounting Flange



**GN 416
Indexing Plunger
Latch Mechanisms**
Guide Zinc Die-Cast /
Plunger Pin Steel



**GN 416.1
Locators**
Zinc Die-Cast,
for Indexing Plunger
Latch Mechanisms
GN 416



**GN 417.1
Locators**
Stainless Steel,
for GN 417 Indexing
Plunger Latch
Mechanisms



**GN 417
Indexing Plunger
Latch Mechanisms**
Zinc Die-Cast,
Non Lock-Out,
with Pull Ring



**GN 417
Indexing Plunger
Latch Mechanisms**
Stainless Steel,
Non Lock-Out, with
Pull Ring / with Wire Loop



**GN 417
Indexing Plunger
Latch Mechanisms**
Zinc Die-Cast,
Lock-Out and
Non Lock-Out, with Knob



**GN 417
Indexing Plunger
Latch Mechanisms**
Stainless Steel,
Lock-Out and
Non Lock-Out, with Knob



**GN 722.6
Indexing Plungers**
Steel,
Non Lock-Out,
with Mounting Flange,
with Pull Ring



**GN 722.6
Indexing Plungers**
Stainless Steel,
Non Lock-Out,
with Mounting Flange,
with Pull Ring



**GN 722.6
Indexing Plungers**
Steel,
Lock-Out,
with Mounting Flange,
with Pull Ring



**GN 722.6
Indexing Plungers**
Stainless Steel,
Lock-Out,
with Mounting Flange,
with Pull Ring



**GN 722.6
Indexing Plungers**
Steel,
Lock-Out,
with Mounting Flange,
with Latch



**GN 722.6
Indexing Plungers**
Stainless Steel,
Lock-Out,
with Mounting Flange,
with Latch



**GN 724.6
Indexing Plungers**
Steel / Stainless Steel,
with Chamfered Pin,
with Mounting Flange



**GN 412.1
Mounting Blocks**
Zinc Die-Cast,
for Indexing Plungers /
Cam Action
Indexing Plungers



**GN 612.2
Cam Action
Indexing Plungers**
Steel,
Lock-Out,
with Mounting Flange



GN 612.9
Cam Action
Indexing Plungers
Zinc Die-Cast,
Lock-Out,
with Mounting Flange



GN 722.3
Cam Action
Indexing Plungers
Steel,
Lock-Out,
with Mounting Flange



GN 722.3
Cam Action
Indexing Plungers
Stainless Steel,
Lock-Out,
with Mounting Flange



GN 724.3
Cam Action
Indexing Plungers
Steel / Stainless Steel,
with Chamfered Pin,
with Mounting Flange



GN 3492
Mounting Blocks
Stainless Steel



GN 1050
Quick Release
Couplings
Aluminum



GN 1050.1
Inserts
Steel,
for Quick Release
Couplings GN 1050



GN 1050.2
Flanges
Steel,
for Quick Release
Couplings GN 1050 and
Inserts GN 1050.1



EN 449.1
Snap Door Latches
Plastic,
Adjustable,
with Cover Caps



EN 449.4
Snap Latches
Plastic,
with Gripping Tray



GN 936
Slam Latches /
Slam Locks
Zinc Die-Cast



GN 4490
Ball Catches
Zinc Die-Cast



GN 4490
Ball Catches
Stainless Steel



GN 4490.1
Mounting Plates
Stainless Steel,
for Ball Housings of
Ball Catches GN 4490



GN 4490.2
Mounting Plates
Stainless Steel,
for Mounting Blocks of
Ball Catches GN 4490



GN 702
Stop Latches
Zinc Die-Cast,
with 4 Indexing Positions



GN 938
Hinges
Zinc Die-Cast,
for Panels (Door Panes)



GN 2295
Triple Leaf Hinges
Aluminum,
for Aluminum Profiles /
Panel Elements



GN 2295
Triple Leaf Hinges
Aluminum,
for Aluminum Profiles /
Panel Elements



GN 2291
Hinge Leafs
Aluminum,
for Aluminum Profiles /
Panel Elements





**EN 159
Hinges**
Plastic,
for Profile Systems



**EN 159.1
Doppel-Hinges**
Plastic,
for Profile Systems



**GN 161
Hinges**
Zinc Die-Cast,
for Aluminum Profiles



**GN 127
Hinges**
Zinc Die-Cast,
Adjustable,
with Alignment Bushings



**GN 127
Hinges**
Stainless Steel,
Adjustable,
with Alignment Bushings



**EN 236
Hinges**
Plastic,
Adjustable,
with Alignment Bushings



**EN 151.4
Hinges**
Plastic,
Adjustable,
with Slotted Holes



**GN 2292
Double Leaf
Lift-Off Hinges**
Aluminum,
for Profile Systems,
with Positioning Guide



**GN 2294
Double Leaf
Lift-Off Hinges**
Aluminum,
for Profile Systems /
Panel Elements



**GN 139.1
Hinges with Integrated
Safety Switch**
Zinc Die-Cast,
with Connector Cable



**GN 139.2
Hinges without Switch**
Zinc Die-Cast,
to Accompany GN 139.1
Hinges with Integrated
Safety Switch



**GN 139.3
Flat Mounting Plates**
Steel,
for Hinges GN 139.1 /
GN 139.2



**GN 139.4
Angled Mounting Plates**
Zinc Die-Cast,
for Hinges GN 139.1 /
GN 139.2



**EN 239.6
Hinges with Integrated
Safety Switch**
Plastic,
with Connector Plug



**EN 239.7
Hinges without Switch**
Plastic,
to Accompany Hinges



**EN 239.8
Flat Mounting Plates**
Plastic,
for Hinges
GN 239.6 / GN 239.7



**EN 239.4
Hinges with
Integrated Switch**
Plastic,
with Connector Plug




**EN 239.3
Hinges without Switch**
Plastic,
to Accompany Hinges



**GN 145
Flanged Mounting
Clamps**
Aluminum,
with 2 Mounting Holes



**GN 145
Flanged Mounting
Clamps**
Stainless Steel,
with 2 Mounting Holes



**GN 146.3
Flanged
Connector Clamps**
Aluminum,
with 2 Mounting Holes



**GN 146.9
Flanged
Connector Clamps**
Plastic



**GN 162.3
Base Plate
Connector Clamps**
Aluminum /
Stainless Steel,
with 2 Mounting Holes



**GN 231
Tube Supports**
Aluminum,
Split Assembly



**GN 271
Swivel Clamp
Connector Bases**
Aluminum



**GN 271
Swivel Clamp
Connector Bases**
Stainless steel



**GN 281
Swivel Clamp
Connector Joints**
Aluminum /
Stainless Steel



**GN 271.4
Sensor Holders**
Aluminum



**GN 473
Base Plate
Mounting Clamps**
Aluminum




**EN 175
Base Plate
Mounting Clamps**
Plastic



**GN 477
Mounting Clamps**
Aluminum



**GN 480
Flanged Mounting Bolts**
Steel,
Connecting Element for
Mounting Clamps



**GN 485
Base Plate Swivel
Mounting Clamps**
Aluminum



**GN 967
Connecting Brackets**
Sheet Steel,
Flat or L-shaped,
for Profile Systems



**GN 3490
Threaded Flanges**
Steel Precision Casting,
for Profile Systems



**GN 939
Panel
Support Clamps**
Zinc Die-Cast



**GN 938.1
T-Nuts**
Zinc Die-Cast,
for GN 938 and GN 939



**EN 649
Panel
Support Clamp**
Plastic



**GN 4470
Magnetic Catches**
Neodymium, Iron,
Boron (NdFeB),
Zinc Die-Cast Housing



**GN 56
Retaining Magnets**
Neodymium, Iron,
Boron (NdFeB),
Plastic Housing

