



Specification

- Screw
 - Steel
 - Heat treated
 - Black oxide finish
- Pad
 - Steel **ST**
 - Plastic **PA**
 - Black Delrin®
- *Plastic Characteristics* → page 2135
- **RoHS compliant**



Information

TS swivel clamp screws securely hold parts with an angled surface without marring or damaging the surface. For use where maximum rigidity is necessary or where space is limited. The pad swivels 7 1/2° in any direction.

see also...

- *Swivel Screw Clamps KHTS (with Knurled Head)* → www.jwwinco.com

How to order TS-10X32-0.34-ST	1 Thread d_1
	2 Length l_2
	3 Pad material

Inch table

Dimensions in: inches - millimeters

d₁	l₂	d₂	l₁	A/F	Maximum load
10 x 32	0.34 8.6	0.146 3.7	0.50 12.7	0.09	500 lbf 2224 N
1/4 x 20	0.34 8.6	0.185 4.7	0.50 12.7	0.13	900 lbf 4003 N
1/4 x 20	0.59 15.0	0.185 4.7	0.75 19.1	0.13	900 lbf 4003 N
1/4 x 20	0.84 21.3	0.185 4.7	1.00 25.4	0.13	900 lbf 4003 N
1/4 x 20	1.34 34.0	0.185 4.7	1.50 38.1	0.13	900 lbf 4003 N
5/16 x 18	0.55 14.0	0.240 6.1	0.75 19.1	0.16	2290 lbf 10186 N
5/16 x 18	0.80 20.3	0.240 6.1	1.00 25.4	0.16	2290 lbf 10186 N
5/16 x 18	1.30 33.0	0.240 6.1	1.50 38.1	0.16	2290 lbf 10186 N
5/16 x 18	1.80 45.7	0.240 6.1	2.00 50.8	0.16	2290 lbf 10186 N
3/8 x 16	0.50 12.7	0.293 7.4	0.75 19.1	0.19	3340 lbf 14857 N
3/8 x 16	0.75 19.1	0.293 7.4	1.00 25.4	0.19	3340 lbf 14857 N
3/8 x 16	1.25 31.8	0.293 7.4	1.50 38.1	0.19	3340 lbf 14857 N
3/8 x 16	1.75 44.5	0.293 7.4	2.00 50.8	0.19	3340 lbf 14857 N
1/2 x 13	0.44 11.2	0.400 10.2	0.75 19.1	0.25	7300 lbf 32472 N
1/2 x 13	0.69 17.5	0.400 10.2	1.00 25.4	0.25	7300 lbf 32472 N
1/2 x 13	1.19 30.2	0.400 10.2	1.50 38.1	0.25	7300 lbf 32472 N
1/2 x 13	1.69 42.9	0.400 10.2	2.00 50.8	0.25	7300 lbf 32472 N
1/2 x 13	2.69 68.3	0.400 10.2	3.00 76.2	0.25	7300 lbf 32472 N
5/8 x 11	0.63 16.0	0.506 12.9	1.00 25.4	0.31	11700 lbf 52044 N
5/8 x 11	1.63 41.4	0.506 12.9	2.00 50.8	0.31	11700 lbf 52044 N
5/8 x 11	2.63 66.8	0.506 12.9	3.00 76.2	0.31	11700 lbf 52044 N
3/4 x 10	1.00 25.4	0.625 15.9	1.50 38.1	0.38	15000 lbf 66723 N
3/4 x 10	2.00 50.8	0.625 15.9	2.50 63.5	0.38	15000 lbf 66723 N
1 x 8	0.83 21.1	0.813 20.7	1.50 38.1	0.56	21000 lbf 93412 N

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

