



Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂	3 Length l						d ₃	h ₁	h ₂
25 0.98	M 4	10 0.39	15 0.59	-	-	-	-	13 0.51	17 0.67	8 0.31
25 0.98	M 5	15 0.59	25 0.98	-	-	-	-	13 0.51	17 0.67	8 0.31
25 0.98	M 6	10 0.39	15 0.59	20 0.79	25 0.98	-	-	13 0.51	17 0.67	8 0.31
35 1.38	M 6	10 0.39	15 0.59	20 0.79	25 0.98	35 1.38	-	18 0.71	20 0.79	8 0.31
35 1.38	M 8	15 0.59	20 0.79	25 0.98	35 1.38	40 1.57	-	18 0.71	20 0.79	8 0.31
35 1.38	M 10	25 0.98	30 1.18	-	-	-	-	18 0.71	20 0.79	8 0.31
45 1.77	M 8	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	22 0.87	26 1.02	12 0.47
45 1.77	M 10	20 0.79	30 1.18	35 1.38	40 1.57	-	-	22 0.87	26 1.02	12 0.47
55 2.17	M 8	15 0.59	20 0.79	30 1.18	40 1.57	-	-	25 0.98	29 1.14	15 0.59
55 2.17	M 10	15 0.59	20 0.79	30 1.18	40 1.57	-	-	25 0.98	29 1.14	15 0.59
55 2.17	M 12	30 1.18	40 1.57	-	-	-	-	25 0.98	29 1.14	15 0.59

Specification

- Eight-lobed knob
Nylon plastic
- Temperature resistant up to 230 °F (110 °C)
- Glass filled
- Black, matte finish
- Threaded stud
Steel, zinc plated
- Plastic Characteristics → page 2135
- RoHS compliant

Information

VPA is an economical but durable eight-lobed knob for many applications.

see also...

- Six-Lobed Knobs VBA (with Brass Tapped Insert) → page 586

How to order 1 2 3 VPA-35-M8-20	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4