

Torque Rating for Plastic Adjustable Levers

WN 300, WN 300.1, WN 303, WN 303.1, and Non-Adjustable Levers WN 400



Size	Arm Length (inches)	Sample	Load to Fracture, lbs.	Torque to Fracture, in.-lbs.	Average Torque to Fracture, in.-lbs.
30	1.18	A	54	135	137.5
		B	56	140	
		C	54	135	
		D	56	140	
45	1.77	A	56	140	155
		B	60	150	
		C	64	160	
		D	68	170	
63	2.48	A	83	250	272.5
		B	90	270	
		C	90	270	
		D	100	300	
78	3.07	A	100	400	415.25
		B	102	410	
		C	102	410	
		D	113	453	
92	3.62	A	91	410	438.75
		B	93	420	
		C	101	455	
		D	104	470	

*Torque Rating for Plastic Adjustable Levers Manufactured After 1/1/2015